


Bridgeport Fittings Inc.

705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Universal Clamp Straps

Images



The one piece clamp back and strap secures both cable and conduit. The UCS-5075 secures 1/2" and 3/4" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin DIA Soated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .710" 0 to 1.10" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043.

Application

Download Photo Image Download Dimensional Image

Dimension A in Inches: 2.42
Dimension B in Inches: 1.47
Dimension C in Inches: .970
Dimension D in Inches: .255

Product Information

Material: Zinc Plated Steel Finish: Zinc Plated

Certifications & Codes:

Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E161206
UL Standard: UL 2239
UNSPSC: 39121705

Catalog ID: UCS-5075

UPC Number: 78174702932

Description: One piece clamp back and strap combination, 1 hole, Steel, 1/2" - 3/4" Trade Size. Patent Pending

Application: The one piece clamp back and strap secures both cable and conduit. The UCS-5075 secures 1/2" and 3/4" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin Coated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .710" 0 to 1.10" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043.

Trade Size: 1/2" - 3/4"

Std Pkg Qty: 250

Unit Qty: 50