

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Universal Clamp Straps

Images





Application

The one piece clamp back and strap secures both cable and conduit. The UCS-75100 secures 3/4" and 1" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin DIA Soated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .925" 0 to 1.32" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043.

Download Photo Image **Download Dimensional Image**

Dimension A in Inches: 2.86 Dimension B in Inches: 1.85 Dimension C in Inches: .973 Dimension D in Inches: .265

Product Information

Material: Zinc Plated Steel Zinc Plated Finish:

Certifications & Codes:

Federal Specification Number: A-A-50553 **NEMA Standard:** FB-1 **UL File Number:** E161206 UL Standard: UL 2239 **UNSPSC:** 39121705

Catalog ID: UCS-75100

UPC Number: 78174702933

Description: One piece clamp back and strap combination, 1 hole, Steel, 3/4" - 1" Trade Size. Patent Pending

Application: The one piece clamp back and strap secures both cable and conduit. The UCS-75100 secures 3/4" and 1"

EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin Coated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .925" 0 to 1.32" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043.

Trade Size: 3/4" - 1"

Std Pkg Qty: 250

Unit Qty: 50