

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Universal Clamp Straps

Images





Dimension A in Inches: 2.86
Dimension B in Inches: 1.85
Dimension C in Inches: .973
Dimension D in Inches: .265

Application

The one piece clamp back and strap secures both cable and conduit. The UCS-5075 secures 3/4" and 1" EMT/Rigid/IMC, Coated EMT/Rigid/IMC, Metallic and DIA Nonmetallic Liquid Tight FMC, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .925" 0 to 1.32" 0 steel and aluminum AC/MC/Jacketed MC cable. Patent Pending

Product Information

Material: Zinc plated Steel, Polyolefin Coating Polyolefin coating over Zinc plated

Finish: Steel

Certifications & Codes:

Federal Specification Number: A-A-50553 NEMA Standard: FB-1 UL Standard: UL 2239 UNSPSC: 39121705

Catalog ID: UCSC-75100

UPC Number: 78174714933

Description: One piece clamp back and strap combination, 1 hole, Steel, 3/4" - 1" Trade Size, Polyolefin Coated

Application: The one piece clamp back and strap secures both cable and conduit. The UCS-5075 secures 3/4" and 1" EMT/Rigid/IMC, Coated EMT/Rigid/IMC, Metallic and Nonmetallic Liquid Tight FMC, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .925" 0 to 1.32" 0 steel and aluminum AC/MC/Jacketed MC cable. Patent Pending

Trade Size: 3/4" - 1"

Std Pkg Qty: 250

Unit Qty: 50