


Stainless Steel



Download Photo Image Dow Dimension A in Inches: 2.42 Dimension B in Inches: 1.47 Dimension C in Inches: .970 Dimension D in Inches: .255

Download Dimensional Image

Application

The one piece clamp back and strap secures both cable and conduit. The UCSS-5075 secures 1/2" and 3/4" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin
DIA Soated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .710" 0 to 1.10" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043. Patented.

Product Information

Material: Stainless Steel

Certifications & Codes:

Federal Specification Number:A-A-50553NEMA Standard:FB-1UL File Number:E161206UL Standard:UL 2239UNSPSC:39121705

Catalog ID: UCSS-5075

UPC Number: 78174702942

Description: One piece clamp back and strap combination, 1 hole, Stainless Steel, 1/2" - 3/4" Trade Size. Patented.

Application: The one piece clamp back and strap secures both cable and conduit. The UCSS-5075 secures 1/2" and 3/4" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin Coated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .710" 0 to 1.10" 0 steel and aluminum AC/MC cable. Plenum Rated for use in Air Handling systems, per UL 2043. Patented.

Trade Size: 1/2" - 3/4"

Std Pkg Qty: 250

Unit Qty: 50

Bridgeport Fittings Inc. 705 Lordship Blvd. Stratford, CT 06615

> Phone: 203-377-5944 Fax: 203-381-3488