








| CATALOG NUMBER   | DESCRIPTION   | UPC CODE     | WEIGHT | CASE QTY | PALLET QTY | NJ | IL | TX | CA | GA  |
|--|---|--------------|--------|----------|------------|----|----|----|----|---|
| <b>Industrial / Hazardous</b>  |   |              |        |          |            |    |    |    |    |   |
| <b>Industrial Emergency</b>  |   |              |        |          |            |    |    |    |    |   |
|    | <b>UEL</b>  |              |        |          |            |    |    |    |    |   |
| UEL1BKSD   | NEMA 4X, WET LOCATION LISTED, 12V, (2) 12W HALOGEN LAMPS, BLACK, SELF DIAGNOSTICS   | 080083508396 | 5.76   | 1        | 144        |    |    |    |    | •   |
| UEL1SD   | NEMA 4X, DIE CAST HOUSING, WET LOCATION LISTED, 12V, (2) 12W HALOGEN LAMPS, SILVER, SELF DIAGNOSTICS                                  | 080083508402 | 13.276 | 4        | 72         | •  | •  | •  | •  | •   |
| UEL1WHSD   | NEMA 4X, WET LOCATION LISTED, 12V, (2) 12W HALOGEN LAMPS, WHITE, SELF DIAGNOSTICS   | 080083508426 | 12.6   | 4        | 96         |    |    |    |    | •   |
|    | <b>UMB1</b>   |              |        |          |            |    |    |    |    |   |
| UMB1   | 6V, (2) 8W INCANDESCENT LAMPS, WET LOCATION LISTED, GREY  | 662400108399 | 10.6   | 1        | 45         |    |    |    |    | • ★   |
| <b>Industrial Exit Signs</b>   |   |              |        |          |            |    |    |    |    |   |
|    | <b>UX</b>   |              |        |          |            |    |    |    |    |   |
| UX61G  | NEMA 4X, LED, DIE CAST ALUMINUM, SILVER HOUSING, WET LOCATION LISTED, SINGLE FACE, GREEN LETTERS, AC ONLY                             | 662400687849 | 9.943  | 4        | 144        |    |    |    |    | •   |
| UX61R  | NEMA 4X, LED, DIE CAST ALUMINUM, SILVER HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, RED LETTERS, AC ONLY                          | 662400687832 | 9.943  | 4        | 144        |    |    |    |    | •   |
| UX61RWH  | NEMA 4X, LED, DIE CAST ALUMINUM, WHITE HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, RED LETTERS, AC ONLY                           | 622696170173 | 4.52   | 4        | 48         |    |    |    |    | •   |
| UX71GWHSD  | NEMA 4X, LED, DIE CAST ALUMINUM, WHITE HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, GREEN LETTERS, SELF-POWERED, SELF-DIAGNOSTICS  | 622696170210 | 4.49   | 4        | 144        |    |    |    |    | •   |
| UX71RBKSD  | NEMA 4X, LED, DIE CAST ALUMINUM, BLACK HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, RED LETTERS, SELF-POWERED, SELF-DIAGNOSTICS    | 622696170227 | 10.049 | 4        | 144        |    |    |    |    | •   |
| UX71RSD  | NEMA 4X, LED, DIE CAST ALUMINUM, SILVER HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, RED LETTERS, SELF-POWERED, SELF-DIAGNOSTICS   | 662400687856 | 10.7   | 4        | 120        |    |    |    |    | •   |
| UX71RWHS   | NEMA 4X, LED, DIE CAST ALUMINUM, WHITE HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, RED LETTERS, SELF-POWERED, SELF-DIAGNOSTICS    | 622696167531 | 4.62   | 4        | 144        |    |    |    |    | •   |
| UX71GSD  | NEMA 4X, LED, DIE CAST ALUMINUM, SILVER HOUSING/FACE, WET LOCATION LISTED, SINGLE FACE, GREEN LETTERS, SELF-POWERED, SELF-DIAGNOSTICS | 662401000838 | 4.496  | 4        | 144        |    |    |    |    | •   |
| UXUK   | CONVERSION KIT - UX EXIT (SILVER) SINGLE TO DOUBLE FACE   | 662400687870 | 0.844  | 1        | 216        |    |    |    |    | •   |
| UXUKWH   | CONVERSION KIT - UX EXIT (WHITE) SINGLE TO DOUBLE FACE  | 622696170241 | 1.768  | 1        | 144        |    |    |    |    | •   |
| <b>Retrofit</b>  |   |              |        |          |            |    |    |    |    |   |
| <b>Fluorescent Emergency Battery Pack</b>  |   |              |        |          |            |    |    |    |    |   |
|  | <b>FBP</b>  |              |        |          |            |    |    |    |    |   |
| FBP3500  | ONE/TWO LAMPS, 1450-3500 LUMENS   | 662401531325 | 10.5   | 2        | 96         |    |    |    |    | •   |
|  | <b>EBP</b>  |              |        |          |            |    |    |    |    |   |
| EBP450X  | FLUORESCENT BATTERY PACK, 450 LUMEN   | 080083561650 | 2.16   | 12       | 768        | •  |    | •  | •  |    |
| EBP700X  | FLUORESCENT BATTERY PACK, 700 LUMEN   | 080083564262 | 2.205  | 12       | 600        |    |    |    |    | •  |

★ Indicates ARRA Eligible Product  Indicates EISA Compliant Pulse Start Products  Indicates Off the Shelf Product

Please reference the Cooper Lighting Stock Guide Terms and Conditions page. Pictures are a representation of product categories and may not illustrate the exact skus listed. Product information is subject to change without notice. Consult factory representative for additional information and inventory details. Visit [www.cooperlighting.com](http://www.cooperlighting.com) for more product information.