Project	Catalog #	Туре	
Prepared by	Notes	Date	



Metalux

UHB LED

LED Round High Bay

Typical Applications

Industrial • Commercial • Retail • Manufacturing • Warehouse • Gymnasium (1) • Multi-purpose • Grocery • High Bay / Low Bay Applications

Note: (1) Rigid Stem mount not recommended for use in gymnasiums.

Interactive Menu

- Order Information page 2
- · Product Warranty

Product Certification









Product Features





Top Product Features

- · LED High Bay fixtures with round form factor designed for various mounting heights and applications
- · Compact, 11" and 14" round die cast aluminum housing
- · White polyester powder coat finish
- · IP65 rated
- · Lumen packages from 12,000 up to 30,000

Dimensional and Mounting Details

UHB-18 8.67" 5.20" 7.69" 6.12" Ø11.33" Ø10.18"





Accessories



ALR Aluminum Reflector



CLR Clear Reflector



WG Wire Guard



Surface Mount Bracket



Metalux

Order Information

SAMPLE ORDER NUMBER: UHB-18-UNV-L840-CD-U

Series	LED Lumen Output	Voltage	CCT	Driver Type	Mounting Type	Packaging
Series (2)	LED Lumen Output	Voltage	ССТ	Driver Type	Mounting Type (1)	Packaging
UHB=LED High Bay	12 =12,000 Lumens 18 =18,000 Lumens 24 =24,000 Lumens 30 =30,000 Lumens	UNV=Universal Voltage 120-277 347V=347 Volt	L840 =4000K L850 =5000K	CD =0-10V Dimming Driver	[Blank]=1/2" Threaded Hub	U =Unit Pack
Notes (2) DesignLights Consortium® Qualified and classified for DLC Premium, refer to www.designlights.org for details.					Notes (1) Rigid Stem mount not recommended for use in gymnasiums.	

Accessories

Accessories	
UHB-CLR10=Clear Polycarbonate Reflector for 12K lumen UHB-CLR12=Clear Polycarbonate Reflector for 18K lumen UHB-CLR14=Clear Polycarbonate Reflector for 24/30K lumen UHB-ALR10=Aluminum Reflector for 12K lumen UHB-ALR12=Aluminum Reflector for 18K lumen UHB-ALR14=Aluminum Reflector for 24/30K lumen UHB-WG10=Wire Guard for 12K lumen UHB-WG10=Wire Guard for 12K lumen UHB-WG12=Wire Guard for 18K lumen UHB-SMB10=Surface Mount Bracket for 12K lumen UHB-SMB10=Surface Mount Bracket for 18K lumen UHB-SMB14=Surface Mount Bracket for 24/30K lumen UHB-SMB14=Surface Mount Bracket for 24/30K lumen	

Product Specifications

· Diecast aluminum housing and heatsink for added protection

Electrical

- · Long-life LED system with electrical driver for optimal performance
- · LED's available in 4000K and 5000K with CRI> 80
- · Available for 120-277V, and 347V applications
- · 0-10V dimming standard
- 72" power and dimming cord provided as standard for easier installation
- · Integral 4K surge protector

Finish

· White polyester powder coat finish painted after fabrication

Optics

· Medium distribution standard

Mounting

- Designed for suspension mounting with 1/2" threaded hub
- · Accessory hook included

Compliance

- · cULus listed for wet location -40C to 45C ambient environments
- IP65 rated
- LED modules comply with IESNA LM-79 and LM-80 testing standards
- · DesignLights Consortium® Qualified and classified for DLC Premium, refer to www.designlights.org for details.

Warranty

· Five year warranty

Energy and Performance Data by Catalog Number

	Performance		
Catalog Number	Delivered Lumens	Watts	Efficacy (lm/W)
UHB-12-UNV-L840-CD-U	13436	99	136
UHB-12-UNV-L850-CD-U	13672	100	137
UHB-18-UNV-L840-CD-U	19607	147	133
UHB-18-UNV-L850-CD-U	19654	150	131
UHB-24-UNV-L840-CD-U	26600	197	135
UHB-24-UNV-L850-CD-U	26664	197	135
UHB-30-UNV-L840-CD-U	32235	236	137
UHB-30-UNV-L850-CD-U	32725	239	137

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours)	Theoretical L70 (hours)
25°C	> 91%	> 218,000

Ambient Ratings

Lumen Package	Ambient Rating
UHB-12	45C
UHB-18	45C
UHB-24	45C
UHB-30	45C

Energy Data

Input Watts:
UHB-12=98W
UHB-18=153W
UHB-24=197W
UHB-30=240W

Shipping Data

•					
Catalog No.	Wt.				
UHB-12	10 lbs.				
UHB-18	10 lbs.				
UHB-24	15 lbs.				
UHB-30	15 lbs.				



