

Eaton UNF405 SA

Catalog Number: UNF405 SA

Eaton Crouse-Hinds series UNF union, Rigid/IMC, Female, Copper-free aluminum, 1-1/4"



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series UNF union	UNF405 SA
UPC	Product Length/Depth
782274101859	2.25 in
Product Height	Product Width
2.75 in	2.75 in
Product Weight	
0.57 lb	

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Conduit type

Rigid/IMC

Gender

Female

Material

Copper-free aluminum

Trade size

1-1/4"

Resources

Catalogs

[Crouse-Hinds series Explosionproof Conduit Unions, Elbows and Tees catalog page](#)

Certification reports

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - UNF405 SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)