

## Eaton meter socket

**UNRRS101BEUSE**

**UPC:**786685217840

**Dimensions:**

- **Height:** 11.05 IN
- **Length:** 3.6 IN
- **Width:** 8.22 IN

**Weight:**7.35 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** 3-5/16 Hub Opening
- **Amperage Rating:** 125A
- **Feed Type:** Overhead
- **Line:** #8-2/0 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Security:** Ring
- **Voltage Rating:** 600V
- **Number Of Sockets:** 1

**Supporting documents:**

- [Dimensional Drawing - METER SOCKET URTRS101\(X\)E, UNRRSS101\(X\)E 125AMP, 1 Ø OH/UG, RINGTYPE](#)
- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - UNRRS101BEUSE](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data





## Eaton meter socket

**UNRRS101BEUSE**

**UPC:**786685217840

**Dimensions:**

- **Height:** 11.05 IN
- **Length:** 3.6 IN
- **Width:** 8.22 IN

**Weight:**7.35 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** 3-5/16 Hub Opening
- **Amperage Rating:** 125A
- **Feed Type:** Overhead
- **Line:** #8-2/0 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Security:** Ring
- **Voltage Rating:** 600V
- **Number Of Sockets:** 1

**Supporting documents:**

- [Dimensional Drawing - METER SOCKET URTRS101\(X\)E, UNRRSS101\(X\)E 125AMP, 1 Ø OH/UG, RINGTYPE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - UNRRS101BEUSE](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data



