

# Specifications



## Eaton UNRRS101BEUSE

Eaton meter socket, 3-5/16 Hub Opening, 125A, Overhead, 3-5/16 Hub Opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UNRRS101BEUSE
<b>UPC</b>	786685217840
<b>PRODUCT LENGTH/DEPTH</b>	3.6 in
<b>PRODUCT HEIGHT</b>	11.05 in
<b>PRODUCT WIDTH</b>	8.22 in
<b>PRODUCT WEIGHT</b>	7.35 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

TYPE	3-5/16 Hub Opening
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TX : CenterPoint Energy (HL&P/Reliant)
LINE	#8-2/0 kcmil
LOAD	#8-2/0 kcmil
ENCLOSURE MATERIAL	16 GA GALV STEEL
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 hub opening
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - UNRRS101BEUSE</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.