

Eaton UNY405

Catalog Number: UNY405

Eaton Crouse-Hinds series UNY union, Rigid/IMC, Male, Feraloy iron alloy, 1-1/4"



General specifications

| | |
|-------------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series UNY union | UNY405 |
| UPC | Product Length/Depth |
| 782274648200 | 3.72 in |
| Product Height | Product Width |
| 2.94 in | 2.94 in |
| Product Weight | |
| 1.91 lb | |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Conduit type

Rigid/IMC

Gender

Male

Material

Feraloy iron alloy

Trade size

1-1/4"

Resources

Catalogs

[Crouse-Hinds series Explosionproof Conduit Unions, Elbows and Tees catalog page](#)

Certification reports

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - UNY405](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)