

UNDERCABINET LIGHTING

PRO-SFRIFS XFNON 20W - 12-volt Xenon Lamps

UPX109

Project:	_
Fixture Type:	
Location:	
Contact/Phone:	

PRODUCT DESCRIPTION

The Pro-Series Xenon modular series with integral electronic transformer operates 12-volt halogen lamps to deliver the best color rendering with maximum light out put and lamp life. The efficient operation of low voltage lamps, along with a unique housing/reflector system, reduces mounting surface temperatures well below what is typical for xenon undercabinet fixtures. Pro-Series Xenon fixtures are optimized for fast permanent installation, mounting either flush to the rear backsplash or to the front lip of cabinetry to suit project conditions and homeowner preference.

PRODUCT SPECIFICATIONS

Lamps 20W-12-volt xenon bi-pin high output lamps supplied with fixture Projected 10,000 hour life based on actual operating voltage in fixture.

Transformer Integral electronic 120 to 12-volt step down transformer is accessible for maintenance without having to remove fixture.

Housing Extruded Aluminum • Designer brushed bronze finish.

Reflector Specular aluminum reflector behind each lamp.

Diffuser Clear prismatic tempered glass lens for maximum light transmission

- Reverse-angled to minimize perceived brightness
- Captive lens has hinged design for tool-less relamping
 Spring loaded retention bar prevents lens from accidently being bumped loose.

Switch Convenient integral Hi/Lo/Off rocker switch.

Dimming For best results use dimmer specifically designed for use with electronic low voltage transformers.

Labels UL Listed.

INSTALLATION


UPX series fixtures optimized with a center rear wiring access compartment and push-in 3-wire electrical connectors for quick electrical connection without having to open the fixture or remove the lens. Rear wiring access compartment covers provided with push-in connector for non-metallic cable and knockout for feed thru wiring capability. Multiple off-center knockouts provided in two, three and four lamp fixtures. Die-cast fitting for 3/8" flexible metal conduit supplied in a hardware pack. Fixtures may be mounted flush to the backsplash or up against the front lip of the cabinetry using captive mounting screws.

Optional Direct Wire Optional direct wire module (UDWM sold separately) facilitates code-compliant installation of fixture at front edge of cabinetry. Supplied with 36" field-shortenable jumper cord to bring power to either end of

Electrically Connecting Multiple Fixtures Up to 10 fixtures may be electrically joined together using the straight joiner connector supplied with each



DIMENSIONS




ENGINEERING DATA

	UPX109
Total input power (watts)	20
Total Operating AMPS	.17
Power Factor	.99
Maximum cabinet bottom contact	temperature: less than 60° C.

PRO-SERIES XENON 5 MINUTE DIRECT-WIRE INSTALLATION







Step 2 Connect supply wires to fixture leads using push-in connectors.



Step 3 Mount fixture to cabinet bottom using captive mounting screws.

ORDERING INFORMATION (Type fixture options in the blank form fields below)

Example: UPX109 BZ

Series		Finish	
UPX109	Pro-Series Xenon Undercabinet, 9" 1 Lamp	BZ	Brushed Bronze


UNDERCABINET LIGHTING

PRO-SERIES XENON 20W - 12-volt Xenon Lamps

UPX109

LIGHTING APPLICATION DATA

FOOTCANDLES ON HORIZONTAL WORK SURFACE



Catalog		Beam Width*	Footcandles			
Numbers	Lamps		A	В	C	D
UPX109	(1) 20-watt Xenon	21"	9	31	28	35

^{*} Beam width defined as 50% of maximum footcandles Rear wall reflectance 50% Counter surface reflectance 20%