



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000



URD2224PCS 2-2-2-4 Urd Dyke Alu PCS

King Wire Inc.

Catalog Number	URD2224PCS
Manufacturer	King Wire Inc.
Description	Type MC Cable, Flame Retardant;Moisture Resistant;Sunlight Resistant Additional Information, Mobile Home Application, Aluminum Alloy Conductor Material, 2-2-2-4 Awg Conductor Size, 100 A Current Rating, Polyethylene (Xlpe) Insulation Material, 60 Mil Insulation Thickness, Made In Usa, +90 °C Maximum Operating Temperature, 0.909 In Outside Diameter, Reel Package Type, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification A-A-59544;Nec Nfpa 70, 2011 Edition;Rohs Compliant;Ul 44;Ul 84 Standards Met,
Weight per unit	0.3590 (lbs/ft)
Product Category	Direct Burial Wire

Descriptions

Description	2-2-2-4 URD DYKE ALU PCS
-------------	--------------------------

Manufacturer Information

Brand	Aluminum
-------	----------

Taxonomies, Classifications, and Categories

Category Description	Direct Burial Wire
----------------------	--------------------

Packaging

Carton	1
Weight Per foot	0.359