

## Eaton meter socket

URTRS101BE

UPC:786685217826

### Dimensions:

- **Height:** 11 IN
- **Length:** 3.63 IN
- **Width:** 8.25 IN

**Weight:**7 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 3 5/16 in hub opening
- **Amperage Rating:** 125A
- **Feed Type:** Overhead
- **Hub Type:** Hub opening
- **Line:** #8-2/0 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Security:** Ring
- **Voltage Rating:** 600V
- **Number Of Sockets:** 1

### Supporting documents:

- [Dimensional Drawing - METER SOCKET URTRS101\(X\)E, UNRRSS101\(X\)E 125AMP, 1 Ø OH/UG, RINGTYPE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - URTRS101BE](#)

### Certifications:

- UL Listed



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.

## Eaton meter socket

URTRS101BE

UPC:786685217826

### Dimensions:

- **Height:** 11 IN
- **Length:** 3.63 IN
- **Width:** 8.25 IN

**Weight:**7 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 3 5/16 in hub opening
- **Amperage Rating:** 125A
- **Feed Type:** Overhead
- **Hub Type:** Hub opening
- **Line:** #8-2/0 kcmil
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Security:** Ring
- **Voltage Rating:** 600V
- **Number Of Sockets:** 1

### Supporting documents:

- [Dimensional Drawing - METER SOCKET URTRS101\(X\)E, UNRRSS101\(X\)E 125AMP, 1 Ø OH/UG, RINGTYPE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - URTRS101BE](#)

### Certifications:

- UL Listed



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.