



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



USB20CPDGY Recp Duplex 20A 125V Usb C PD Gy

Hubbell Wiring Devices

Catalog Number	USB20CPDGY
Manufacturer	Hubbell Wiring Devices
Description	Tamper Resistant Receptacle, 2-Pole 3-Wire Grounding, 1 Type "C" Power Delivery, 1 Type "C" Standard 5V
Weight per unit	0.4000 (lbs/each)
Product Category	Wiring Devices

Features

Number of Wires	3-Wire
pallet quantity	3000
Poles	2-Pole
Voltage Rating	125 V

Descriptions

Description	RECP DUPLEX 20A 125V USB C PD GY
extra long description	HWDK USB20CPDGY RCPT DUP 20A 125V U
Features	USB Charger Receptacles and Outlets - More Ways to Charge Faster with Hubbell's line of Power Delivery USB Chargers, available in Type-C and Combination Type A&C, all with a USB high power output of 55 Watt 20 Volt DC. Hubbell's USB Charger Duplex Receptacle provides both USB and electrical power in a standard single gang opening. Designed to provide maximum charging for portable electronics, the USB ports are capable of charging two tablets simultaneously OR one laptop at up to 20V and one phone.
Long Description	Tamper Resistant Receptacle, 2-Pole 3-Wire Grounding, 1 Type "C" Power Delivery, 1 Type "C" Standard 5V
Product Type	RCPT Dup 20A 125V Usb C PD Gy

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585723235
Manufacturers Part Number	USB20CPDGY
series	USB Charger
UPC	783585723235

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	USB



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.4

Uses, Certifications, and Standards

nema rating	5-20R
standard	NEMA 5-20R, USB PD 3.0, USB BC1.2