



Catalog No. UTH7330TMEP

Description: 320 AMP OH/UG 3-PHASE MTR SKT

UPC No 784567721867

Home > Single Socket Metering > Single Socket Metering

METER SOCKET-(1) 320A 600V 3P4W G90 N3R 7-TERM LARGE HUB OPENING LEVER BYP TRIPLEX GRD TOP/BOT FEED

Descriptors

Category	Single Socket Metering
----------	------------------------

Specifications

Phase	3
Voltage	600
Amps	320
Hub Type	Large Hub Opening
# of Terminals	7
Lever Bypass	Yes
Horned Bypass	No
Socket Type	Ringless
Enclosure Type	N3R
Metal Type	G90 Steel
Overhead/ Underground Line Feed	Top/Bottom
Wire Range (Cu/Al)	Studs - (1) 600MCM or (2) 350MCM
Triplex Ground	Yes

Publications

Title	Publication No.	Publication Type
Outline Drawing for Part # UTH7330TMEP METER SOCKET-(1) 320A 600V 3P4W G90 N3R 7-TERM LARGE HUB OPENING LEVER BYP TRIPLEX GRD TOP/BOT FEED	UTH7330TMEP	Drawings-Outline and Dimensional

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.