

Specifications



Photo is representative



Eaton V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T15
UPC	786680035234
PRODUCT LENGTH/DEPTH	16.5 in
PRODUCT HEIGHT	32.02 in
PRODUCT WIDTH	23 in
PRODUCT WEIGHT	181 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Physical Attributes

COIL MATERIAL	Aluminum
DESIGN	DT-3
FRAME	912B
TAP SIZE	2 at +2.5% FCAN, 4 at -2.5% FCBN
TYPE	Dry Type Distribution Transformer

Miscellaneous

WEATHERSHIELD	WS38
----------------------	------

Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	15 kVA
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208Y/120 V
TEMPERATURE RISE	150 °C rise

Resources

CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T15

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest
product and support information.