

FEATURES & SPECIFICATIONS

Utility wall-, ceiling- or pendant-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications. Incandescent, fluorescent, metal halide or high pressure sodium sources are available.

Rugged die-cast aluminum housing with heavy-duty glass globe. 3/4" threaded knockouts allow for side or top conduit entry. Gray finished.

Designed for easy installation and maintenance.

Prismatic globe for even distribution.

Junction box included

LISTINGS

Listed and labeled to UL standards for wet locations. Listed and labled to CSA standards.

WARRANTY

2-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Specifications

All dimensions are inches (centimeters) unless otherwise indicated.


VC150I

Ceiling



Height: 9 (22.9) Width: 4-1/2 (11.4)

Wall



Height: 10 (25.4) Width: 7-1/4 (18.4)

VW150I

Catalog Notes Туре

Utility Vapor Tights







ORDERING INFORMATION

Catalog Number	UPS	Description	Lamp Wattage	Source	Lamp Voltage	Lamp Included	Pallet (lbs)	Standard Carton Qty	Qty
VC150I M12	745973817704	Ceiling mount	150	Incandescent	120	N	2	288	12
VW150IM12	745973817681	Wall Mount	150	Incandescent	120	N	2	192	12