



VHB18WUNVL840CDU 134W Led Highbay 40K 18000LM Dim 120-277V Wide

Cooper Lighting Solutions

Catalog Number	VHB18WUNVL840CDU
Manufacturer	Cooper Lighting Solutions
Description	Value High Bay, 18K Lumen, Wide Dist, 120-277V, 4000K, Dim
Weight per unit	13.5 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.36 (at 277V)
Ballast Type	N/A
Lamp Type	LED
Material	Aluminum
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	134W LED HIGHBAY 40K 18000LM DIM 120-277V WIDE
extra long description	CLS VHB-18-W-UNV-L840-CD-U VHB 1800
Long Description	Value High Bay, 18K Lumen, Wide Dist, 120-277V, 4000K, Dim
Product Type	VHB 18000LM W Unv 4000K CD U
Special Features	Compact, lightweight design for ease of installation

Manufacturer Information

Brand	METALUX
GTIN	00080083785919
Manufacturers Part Number	VHB-18-W-UNV-L840-CD-U
UPC	080083785919

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	13.45

Uses, Certifications, and Standards

Application	lighting
Mounting	High Bay
standard	cULus Listed - Damp Location;40 Degree C Ambient Temperature Rating;RoHS Compliant;LM79/LM80 Compliant;DLC Qualified