
VHB LED High bay luminaire

Metalux







[371mm]



VHB LED high bay

The **VHB** is designed for a wide variety of applications and mounting heights with a balance of fixture performance and affordability. Precision-designed optics, multiple distributions, lumen outputs and color temperatures make the VHB ideal for industrial, commercial, manufacturing, gymnasium and other applications that utilize traditional linear fluorescent and HID high bays. The proprietary discrete, low-brightness LED module assembly offers exceptional optical performance with the enhanced benefits of LED lighting, including energy savings, extended system life, and reduced carbon footprint.

Perfect for renovation or new construction! Ideal one-for-one replacement! No maintenance required!

Bottom line savings and industry leading performance!



Metalux

2-13/16" [71mm]

Compact and durable construction

- Extruded aluminum and CRS construction for added durability
- Compact 15" x 18" low-profile housing
- Precision-designed, high-impact polycarbonate optics
- Suspension mountable with V-Hangers (supplied)

Energy saving LED

- Up to 65% energy savings
- Optional sensor for added energy savings
- No relamping required
- 12' 30' mounting heights

Construction

VHB high bay


	Compact 15" x 18" design for ease of installation
	Durable extruded aluminum and CRS construction
	High-impact polycarbonate lens protects LEDs
	Five lumen packages (9,000, 12,000, 15,000, 18,000, 24,000)
	ldeal for 12' - 30' mounting heights
	Suspension mountable with V-Hangers (supplied)
	Optional single-point mounting kit reduces installation time
	Easy one-for-one replacement
	Optional wire guard for added protection

Mounting

VHB-SPM=Single	FH-1 =2-1/2"	FL-1 =2-1/2"	HBAYC-CHAIN/SET/U=	Y-Toggle =
point mount adapter	fixture	fixture	Hook style mounting	Mounting toggle
kit	hook	loop	chain set	and cable
	Ç	Q	·	×+

Compliance and approvals








Innovation you can rely on[™]

HOME B:00 GUEST

Performance

	VHB high bay
	Up to 65% energy savings compared to traditional high bay fixtures
High-performance efficacy up to 133 lumens per watt	
	Three Correlated Color Temperatures (3500K, 4000K, 5000K) at typical 85 CRI
	Precision optics in Narrow and Wide distribution
	Lumen maintenance of L83 @ 60,000 hours
	Optional sensor control for added energy savings
	Binning: Per ANSI, 3-step MacAdam elipse

Photometrics



Energy data

Catalog number	Delivered lumens	Watts	Efficacy (Im/W)
Narrow			
VHBLED-LD1-9-N-UNV-L840-CD1-U	8885	70	127
VHBLED-LD1-9-N-UNV-L850-CD1-U	8999	70	129
VHBLED-LD1-12-N-UNV-L840-CD1-U	12374	100	124
VHBLED-LD1-12-N-UNV-L850-CD1-U	12533	100	125
VHBLED-LD1-15-N-UNV-L840-CD1-U	15020	124	121
VHBLED-LD1-15-N-UNV-L850-CD1-U	15213	124	123
VHBLED-LD1-18-N-UNV-L840-CD1-U	18323	160	115
VHBLED-LD1-18-N-UNV-L850-CD1-U	18559	160	116
VHBLED-LD1-24-N-UNV-L840-CD1-U	23292	213	109
VHBLED-LD1-24-N-UNV-L850-CD1-U	23592	213	111
Wide			1
VHBLED-LD1-9-W-UNV-L840-CD1-U	9004	70	129
VHBLED-LD1-9-W-UNV-L850-CD1-U	9341	70	133
VHBLED-LD1-12-W-UNV-L840-CD1-U	12540	100	125
VHBLED-LD1-12-W-UNV-L850-CD1-U	13009	100	130
VHBLED-LD1-15-W-UNV-L840-CD1-U	15221	124	123
VHBLED-LD1-15-W-UNV-L850-CD1-U	15417	124	124
VHBLED-LD1-18-W-UNV-L840-CD1-U	18568	160	116
VHBLED-LD1-18-W-UNV-L850-CD1-U	19263	160	120
VHBLED-LD1-24-W-UNV-L840-CD1-U	23604	213	111
VHBLED-LD1-24-W-UNV-L850-CD1-U	23908	213	112

Optional advanced technology

Integrated sensor technology	LumaWatt Pro
<i>INtuitive, INtelligent, INtegrated.</i> Combining the control within the light fixture reduces installation and design time; while meeting energy codes.	LumaWatt Pro powered by Enlighted is an integrated system of luminaires, digital sensors, and application-based software for any size project. LumaWatt Pro Connected Lighting Wireless System





Innovation you can rely on

3

Lighting Product Lines	Controls Product Lines Greengate
Halo Commercial	iLumin
Portfolio	Zero 88
Iris	Fifth Light Technology
RSA	iLight (International Only)
Metalux	
Corelite	
Neo-Ray	
Fail-Safe	
MWS	
Ametrix	
Shaper	
io	
Lumark	
McGraw-Edison	
Invue	
Ephesus	
Lumière	
Streetworks	
AtLite	
Sure-Lites	



Eaton 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172 © 2017 Eaton All Rights Reserved Printed in USA Publication No. BR507010EN November 16, 2017 Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.