




NOTES:

1. NOMINAL IMPEDANCE: 75 ohms
2. F-CONNECTOR TYPE: ANSI/SCTE COMPLIANT SEALED BRASS
3. POWER REQUIREMENTS: NONE
4. INPUT CONNECTIONS: 1
5. OUTPUT CONNECTIONS: 4
6. OPERATING TEMPERATURE: -40° TO 60°C
7. INSERTION LOSS: 7dB



PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED
IN THIS DRAWING IS THE SOLE
PROPERTY OF On-Q/LEGRAND.
ANY REPRODUCTION IN PART OR
AS A WHOLE WITHOUT THE WRITTEN
PERMISSION OF On-Q/LEGRAND
IS PROHIBITED. DRAWING IS SUBJECT
TO CHANGE WITHOUT NOTICE.

on·Q

legrand

P.O. Box 60907
Middletown, PA 17106-0907
1-800-321-2343

TITLE:

**1 X 4 ENHANCED PASSIVE VIDEO
SPLITTER/COMBINER**

SIZE

A

DWG NO

VM1000

FILE NAME

CD-VM1000

CUST REV

1

REVISED DATE

11/06/07

SCALE




NONE

SHEET

1 OF 1

NOTES:

- 1. NOMINAL IMPEDANCE: 75 ohms
- 2. F-CONNECTOR TYPE: ANSI/SCTE COMPLIANT SEALED BRASS
- 3. POWER REQUIREMENTS: NONE
- 4. INPUT CONNECTIONS: 1
- 5. OUTPUT CONNECTIONS: 4
- 6. OPERATING TEMPERATURE: -40° TO 60°C
- 7. INSERTION LOSS: 7dB



PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED
IN THIS DRAWING IS THE SOLE
PROPERTY OF On-Q/LEGRAND.
ANY REPRODUCTION IN PART OR
AS A WHOLE WITHOUT THE WRITTEN
PERMISSION OF On-Q/LEGRAND
IS PROHIBITED. DRAWING IS SUBJECT
TO CHANGE WITHOUT NOTICE.

on·Q



P.O. Box 60907
Middletown, PA 17106-0907
1-800-321-2343

TITLE: 1 X 4 ENHANCED PASSIVE VIDEO SPLITTER/COMBINER			
SIZE A	DWG NO VM1000	FILE NAME CD-VM1000	CUST REV 1
REVISED DATE 11/06/07		SCALE NONE	SHEET 1 OF 1