COOPER LIGHTING SOLUTIONS - ALL-PRO^{TT}

DESCRIPTION

The ALL-PRO[™] Vapor tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture is wet location rated and vapor tight to protect against dust and moisture. Perfect for patios, garages, storage, and industrial areas.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing and guard provides protection against vandalism
- Vapor tight protects against dust and moisture
- Suitable for wall or ceiling mounting application
- Removable glass lens
- 1/2" conduit openings on top and sides

- . .
- Electrical operating voltage 120VAC 50/60HZ
- Fixture operating temperature range from

Electrical

- -20°C to 40°C • cULus listed for wet
- locations
- Minimum 125°C supply conductors

Optics

• 100W (maximum) incandescent bulb (sold separately)


Warranty


• 2 year limited warranty




VAPOR TIGHT FLOODLIGHT

DIMENSIONS





ORDERING INFORMATION





Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770.486.4800 www.cooperlighting.com

Specifications and dimensions subject to change without notice.

PS502042EN 2016-12-01

CERTIFICATION DATA cULus Wet Location Listed

TECHNICAL DATA -20°C to 40°C Temperature Rating

TECHNICAL INFORMATION

Model Number	Description	Voltage (V)	Power (W)	Lamp Lumens	Color Temperature (K)	CRI
VT100G	ALL-PRO Vapor Tight Floodlight	120V	100W	1600	2700K	100



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770.486.4800 www.cooperlighting.com

Specifications and dimensions subject to change without notice.