

DESCRIPTION

The ALL-PRO™ Vapor tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture is wet location rated and vapor tight to protect against dust and moisture. Perfect for patios, garages, storage, and industrial areas.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing and guard provides protection against vandalism
- Vapor tight protects against dust and moisture
- Suitable for wall or ceiling mounting application
- Removable glass lens
- 1/2" conduit openings on top and sides

Electrical

- Electrical operating voltage 120VAC 50/60HZ
- Fixture operating temperature range from -20°C to 40°C
- cULus listed for wet locations
- Minimum 125°C supply conductors

Optics

- 100W (maximum) incandescent bulb (sold separately)


Warranty

- 2 year limited warranty




VAPOR TIGHT FLOODLIGHT

DIMENSIONS



ORDERING INFORMATION

Sample Number: VT100G



CERTIFICATION DATA

cULus Wet Location Listed

TECHNICAL DATA

-20°C to 40°C Temperature Rating

TECHNICAL INFORMATION

Model Number	Description	Voltage (V)	Power (W)	Lamp Lumens	Color Temperature (K)	CRI
VT100G	ALL-PRO Vapor Tight Floodlight	120V	100W	1600	2700K	100