



Die cast aluminum construction. Wall bracket plus junction box with sturdy mounting lugs. Medium base socket, 1/2" or 3/4" NPS hub size and a variety of globes. incandescent lamp A21 for 100 series, PS25 for 200 Series. Lamp not supplied.

Color: Natural

Weight: 3.4 lbs

Project:	Туре:
Prepared By:	Date:

Lamp Info		Ballast Info	)
Туре	A21	Туре	N/A
Watts	150W	120V	N/A
Shape/Size	N/A	208V	N/A
Base	N/A	240V	N/A
ANSI	N/A	277V	N/A
Hours	N/A	Input Watts	N/A
Lamp Lumens	N/A		
Efficacy	N/A		

# **Technical Specifications**

## Compliance

## **UL Listed:**

Suitable for wet locations. Suitable for use in dwellings. Suitable for use with 90°C supply wiring. Complies with UL Standard 1598. For non-hazardous locations where the lamp, socket and wiring require protection from rain, corrosive fumes, noncombustible dusts, moisture, non-explosive vapors and gases.

## Electrical

#### Wattage:

See catalog number chart for maximum wattage with clear glass, colored glass and Permaglobes

#### Socket:

Premium porcelain with 150°C 8" leads attached. Fastened with 2 stainless steel screws.

#### **Maximum Watts:**

150 watts

#### Colored Globe Maximum Watts:

100 watts

## Construction

## Globes:

Supplied with clear heat resistant glass globes unless otherwise stated. Colored and white glass globes available. Unbreakable RAB Permaglobes available in clear and in color.

## **Optional Reflectors:**

Highly reflective white baked polyester epoxy powder finish over a heavy gauge aluminum base. Reflectors thread onto fixtures. See RV series.

#### Die Cast Guard:

Supplied with one piece die cast guard with set screw


#### Other

## **Buy American Act Compliance:**

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

VXBR100DG





#### **Features**

Set screw keeps guard securely in place

Junction box with sturdy mounting lugs

All stainless steel hardware

Close-up plugs allow Phillips or slotted screwdrivers for easy installation

High temperature silicone internal gaskets

Premium porcelain socket with 150C 8" long leads attached