

Wrap-Around Gel Splice Kits

WAGS SERIES



FEATURES

- Wrap-around gel splice closure sleeves quickly insulate and seal buried electrical connections rated up to 1,000 volts.
- Engineered to handle direct burial and manhole applications, these splice enclosure sleeves are equally well suited for insulation and jacket repair.
- Simply wrap and snap the sleeve on any cable in the use range.
- The sealant gel in the sleeve seals on contact.
- The splice closure sleeve can be applied on all common compression connectors and low voltage cables, as well as in-line mechanical connectors.

RATINGS

APPLICATION:

Qualified to ANSI C119.1-1986 for underground splicing.

RATING:

Insulate and seal buried electrical connections rated up to 1,000 volts.

A minimum seal length is required on each side of the connector opening or jacket damage.

Use these guidelines for minimum seal distance:

WAGS-4/0 series: 1.50" each side

WAGS-500 series: 2.00" each side

WAGS-750 series: 3.00" each side

All dimensional data is listed in inches.

CAT. NO.	CONDUCTOR SIZE	GENERAL USE DIA. LENGTH	SLEEVE LENGTH	MAX. CONDUCTOR OPENING	STD. CTN. QTY.
WAGS-4/0-4	4/0-14 AWG	0.15-0.70 (4-18)	4.00 (100)	1.00 (25)	3
WAGS-4/0-6	4/0-14 AWG	0.15-0.70 (4-18)	6.00 (150)	3.00 (75)	3
WAGS-4/0-8	4/0-14 AWG	0.15-0.70 (4-18)	8.00 (200)	5.00 (125)	3
WAGS-4/0-10	4/0-14 AWG	0.15-0.70 (4-18)	10.00 (250)	7.00 (175)	3
WAGS-500-8	500 MCM-6 AWG	0.30-1.30 (10-33)	8.00 (200)	4.00 (100)	3
WAGS-500-10	500 MCM-6 AWG	0.30-1.30 (10-33)	10.00 (250)	6.00 (150)	3
WAGS-750-10	750-250 MCM	0.80-1.50 (20-38)	10.00 (250)	4.00 (100)	3
WAGS-750-14	750-250 MCM	0.80-1.50 (20-38)	14.00 (355)	4.00 (100)	3