



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291



WCM3212T 5HP, 3450RPM, 3PH, 60HZ, 182TCZ, 3623M, Opsb

Baldor/Abb Motors & Mechanical

Catalog Number	WCM3212T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Electric Motors, Pump, Three Phase, Close Coupled, Open Drip Proof, Horsepower: 5, RPM: 3450, Frame Size: 182TCZ, Voltage Rating: 208-230/460 Vac, Rotation: Counter Clockwise, Bearings: Ball, Service Factor: 1.15, Enclosure Type: Open Dripproof, Thermal P
Weight per unit	71.0 (lbs/each)
Product Category	20070327141947

Features

Base	Rigid
frame	182 EA
horsepower	5 in
Insulation Class	F
Phase	3 in
Power Factor	0.89 in
Service Factor	1.15 lb
Speed Rating	3,450 rpm
Voltage Rating	208/230/460 V

Descriptions

Description	5HP,3450RPM,3PH,60HZ,182TCZ,3623M,OPSB
extra long description	BALDOR WCM3212T 5HP,3450RPM,3PH,60H
Long Description	Electric Motors, Pump, Three Phase, Close Coupled, Open Drip Proof, Horsepower: 5, RPM: 3450, Frame Size: 182TCZ, Voltage Rating: 208-230/460 VAC, Rotation: Counter Clockwise, Bearings: Ball, Service Factor: 1.15, Enclosure Type: Open Dripproof, Thermal P
Product Type	5HP, 3450RPM, 3PH, 60HZ, 182TCZ, 3535M, Opsb, F
Special Features	5HP,3450RPM,3PH,60HZ,182TCZ,3535M,OPSB,F

Manufacturer Information

Brand	BALDOR
GTIN	00781568113912
Manufacturers Part Number	WCM3212T
UPC	781568113912

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291

Packaging

Carton	1
Weight Per each	71

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	OPSB
Frequency Rating	60 Hz
Mounting	F1