



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF4ADJSWW590CRIM 4" 10W Led Gimbal Wafer 27K/3K/35K/4K/5K White *Lithonia Lighting*

Catalog Number	WF4ADJSWW590CRIM
Manufacturer	Lithonia Lighting
Description	The Juno 4 Inch Adjustable Downlight With 5CCT Switchable White Technology Provides High-Quality Light Output and Efficiency Featuring A Switch For Easy Color Temperature Adjustment to Choose Between 2700K, 3000K, 3500K, 4000K, or 5000K. The Canless Design Eliminates The Need For Recessed Housings, Making It Easy to Install and Requires Less Labor. The Adjustable Gimbal Allows For Up to 20 Degrees Of Rotation, Making This Version Perfect For Angled Ceilings.
Weight per unit	0.9900 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	5.3x5.3x1.4 IN
dimmable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	720 lm
Material	Polycarbonate
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	9.99

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate
Style	CONTEMPORARY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.4
Length	5.3
Width	5.3

Descriptions

Construction	Canless,New Construction,Remodel
Description	4" 10W LED GIMBAL WAFER 27K/3K/35K/4K/5K WHITE
extra long description	LITH WF4 ADJ SWW5 90CRI MW M6 4IN w
Features	Contractor Select
Long Description	The Juno 4 inch adjustable downlight with 5CCT switchable white technology provides high-quality light output and efficiency featuring a switch for easy color temperature adjustment to choose between 2700K, 3000K, 3500K, 4000K, or 5000K. The canless design eliminates the need for recessed housings, making it easy to install and requires less labor. The adjustable gimbal allows for up to 20 degrees of rotation, making this version perfect for angled ceilings.
Product Type	Downlight

Manufacturer Information

Brand	JUNO
GTIN	00196183148025
Manufacturers Part Number	WF4 ADJ SWW5 90CRI MW M6
UPC	196183148025

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Package	6
Weight	0.8
Weight Per each	0.99

Uses, Certifications, and Standards

Application	Decorative,Hospitality,Residential,Retail,Shower
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8