



CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS							
						NJ	IL	TX	CA	GA			
F-BAY 2HB						NJ	IL	TX	CA	GA			
	2HB15	2'X4' HIGH BAY, 6 LAMP 54W T5HO ELECTRONIC BALLAST (2) W/850 LAMPS, UP-LIGHT AND TOP CONNECTOR BOX PLATE	623961742668	33.2	1	9	•	•	•	•	•	+	
	2HB45	2'X4' HIGH BAY, 6 LAMP 32W T8 ELECTRONIC BALLAST HBF (2) W/850 LAMPS, UP-LIGHT AND TOP CONNECTOR BOX PLATE	623961743351	29.7	1	9	•	•	•			•	+
	2HB-632-UNV-EB82/PLUS-U	2'X4' HIGH BAY, 6 LAMP 32W T8 ELECTRONIC BALLAST HBF (2)	623961148910	27.5	1	9	•						
	2HB-632-UNV-EB82/PLUS-UPL-U	2'X4' HIGH BAY, 6 LAMP 32W T8 ELECTRONIC BALLAST HBF (2) W/UP-LIGHT	623961230714	27.5	1	9		•					
	2HB-632-UNV-EB82-U	2'X4' HIGH BAY, 6 LAMP 32W T8 ELECTRONIC BALLAST (2)	622696768172	27.5	1	9						•	
	2HB632-UPL-L5HO	2HB, F-BAY, 6 LAMP T8 ELECTRONIC BALLAST HBF (2) W/850 LAMPS WITH UPLIGHT	623961373848	27.5	1	9		•					
	2HB-654T5-UNV-EBT2-U	2'X4' HIGH BAY, 6 LAMP 54W T5HO ELECTRONIC BALLAST (2)	622697276256	27.5	1	9	•				•	•	
	2HB-654T5-UNV-EBT2-UPL-U	2'X4' HIGH BAY, 6 LAMP 54W T5HO ELECTRONIC BALLAST (2) W/UP-LIGHT	622696809998	33.2	1	9		•				•	
	2HB75	2'X4' HIGH BAY, 6 LAMP 32W T8 ELECTRONIC BALLAST HBF (2) W/850 LAMPS AND TOP CONNECTOR BOX PLATE	623961743887	33.2	1	9		•	•				


F-BAY HB / 2HB ACCESSORY

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS							
						NJ	IL	TX	CA	GA			
	GRIPPLE-Y-10	MOUNTING TOGGLE & 10' #2 CABLE	623961528552	0.46	50	2000	•	•	•	•	•		
	HB END PLT SUB-ASY W/MOTION SENSOR	HB PLT WITH MOTION SENSOR	623961028380	0.26	50	10000	•	•			•	•	
	HB-FRM/CL PK	HB SERIES FRAME & CLEAR ACRYLIC LENS	622697554590	6.15	2	54	•	•	•	•	•		
	HB-FRM/CL-G2 PK	HB DOORFRAME WITH CLEAR LENS AND G2 GASKET	623961509179	6.15	2	200						•	
	HB-FRM/LENS PK	HB DOORFRAME WITH CLEAR LENS	622697257408	6.15	2	54					•		
	HB-SPS	SINGLE POINT SUSPENSION CABLE KIT	623961227776	0.2	4	4						•	
	HB-TCB-KIT-NO-PLATE-U	TOP CONNECTOR BOX NO PLATE	623961744907	0.26	5	120	•	•	•	•	•		
	HB-TCB-KIT-U	TOP CONNECTOR BOX W/PLATE AND AYC	622697520106	0.26	5	120	•					•	
	RH-1	RETROFIT HANGER W/TOGGLE NUT AND CARRIAGE BOLT	623961832178	0.3	1	550	•	•	•	•	•		
	SWG/HB-4FT-B	HB SERIES FRAMELESS WIREGUARD	623961735240	1.5	20	120	•	•	•			•	
	SWG/2HB-4FT-B	2HB SERIES FRAMELESS WIREGUARD	623961735257	1.5	1	180	•	•	•			•	
	2HB-FRM/CL PK	2HB SERIES FRAME & CLEAR ACRYLIC LENS	622697496159	11.05	2	16	•	•	•	•	•		
	2HB-FRM/CL-G2 PK	2HB SERIES FRAME W/G2 GASKET & CLEAR ACRYLIC LENS	623961509193	8.2	1	200						•	
	2HB-FRM/LENS/WG PK	2HB SERIES FRAME, CLEAR ACRYLIC LENS, & WIREGUARD	622697177416	20.1	2	16						•	
	2HB-FRM/WG PK	2HB SERIES FRAME & WIREGUARD	622697242695	8	2	8		•					
	2HB-4-A W/FRM PK	2HB SERIES FRAME & PRISMATIC ACRYLIC LENS	622696761111	8.2	2	16						•	
	FH-1	FIXTURE HOOK 2-1/2"	662400121244	0.23	10	6300	•	•	•	•	•	•	+
	FL-1	FIXTURE LOOP 2-1/2"	662400121251	0.6	10	6300	•	•	•	•	•	•	+

HEAVY DUTY

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS						
						NJ	IL	TX	CA	GA		
2 LAMP 4'						NJ	IL	TX	CA	GA		
	DIM-232-UNV-EB81-U	2 LAMP, 4' HEAVY INDUSTRIAL, ELECTRONIC BALLAST, T8	662401732760	22.31	1	30		•			•	
ACCESSORY												
	DI-RS-49-B	49-3/4" INDUSTRIAL APERTURED REFLECTOR FOR USE W/RAPID START CHANNELS ONLY FOR DIM	662400107118	7	4	16						•
	WG/DI-4FT-B	4' WHITE WIRE GUARD FOR USE W/ DI, DCI, DIM, DCIM, DIVM & DCIVM SERIES ONLY	662400106616	1.5	12	180		•			•	•

LIGHT-DUTY

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	DISTRIBUTION CTRS						
						NJ	IL	TX	CA	GA		
IA SERIES						NJ	IL	TX	CA	GA		
	IA-232-UNV-EB81-U	2 LAMP, 4' APERTURED UPLIGHT INDUSTRIAL, ELECTRONIC BALLAST, T8	662400234272	15.55	1	60		•			•	•
	IA-296HO-120V-EB21-U	2 LAMP, 8' APERTURED UPLIGHT, INDUSTRIAL, HIGH OUTPUT, T12, ELECTRONIC BALLAST	62396112508	22.91	1	48	•	•				•
	8TIA-232-UNV-EB81-U	4 LAMP, TANDEM 8' INDUSTRIAL APERTURED UPLIGHT, ELECTRONIC BALLAST, T8	662400766612	22.401	1	48		•			•	•