



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WGH100H 100W MH WP Quad-Tap W/ Lamp *Hubbell Lighting, Inc.*

Catalog Number	WGH100H
Manufacturer	Hubbell Lighting, Inc.
Description	
Weight per unit	11.0 (lbs/each)
Product Category	Hid Wallpacks

Features

Lamp Type	PULSE START METAL HALIDE
Material	ALUMINUM
Number of Lamps	1 PH
Voltage Rating	120/220/240/277 VAC

Material, Color, and Finish

Color	Dark Bronze
fixture material	aluminum
Style	Glass Wallpack - Horizontal Lamp

Descriptions

Description	100W MH WP QUAD-TAP W/ LAMP
Product Type	Walpak 100W MH 120V Glass BRZ W/LP

Manufacturer Information

Brand	Hubbell Outdoor Lighting
GTIN	00785988465859
Manufacturers Part Number	WGH-100H
UPC	785988465859

Taxonomies, Classifications, and Categories

Category Description	Outdoor HID Lighting
Type	Wallpack

Packaging

Carton	1
Weight Per each	11

Uses, Certifications, and Standards

Application	Perimeter Wallpack
Frequency Rating	50/60 HZ
Mounting standard	Wall (surface) UL mA

WGH SERIES

GLASS WALLPACKS

Cat.#

Job

Type



HUBBELL
Outdoor Lighting

Approvals

INTENDED USAGE

- Perimeter lighting for safety and security. Use on factories, warehouses, self storage, commercial buildings, etc.

CONSTRUCTION

- Borosilicate glass refractor softens lamp image and provides uniform distribution – 4 times spacing to mounting height.
- Cast aluminum frame holds lens and seals to housing gasket with two stainless steel screws.
- Door assembly hinges to side on mid-size units; hinges down on large units
- Cast aluminum housing with 1/2" conduit entries, button photocontrol can be field installed
- All units have dark bronze powder paint finish, Quad-Tap® ballasts and lamps included

ELECTRICAL

- WGH mid-size is 150w HPS/PS and 84w CFL; large size handles 250-400w PS and HPS; 150P unit includes medium base lamp; All other HID units include mogul base lamp

LISTINGS


- Listed to UL1598 for use in wet locations




MID-SIZE



LARGE



	A	B	C	D	E
MID-SIZE	9"	7 1/4"	13"	6.5"	2.5"
	229 mm	184 mm	330 mm	165mm	63.5mm
LARGE	9"	13"	17"	-	-
	229 mm	330 mm	432 mm	-	-



ORDERING INFORMATION

Catalog Number ¹	Wattage/Source	Voltage	Finish	Weight	
				lbs	kg
MID-SIZE SERIES					
WGH-150P	150w/PS	120, 208, 240, 277V	Bronze	19	8.6
WGH-150S120	150w/HPS	120V	Bronze	15	6.8
LARGE SERIES					
WGH-250P	250w/PS	120, 208, 240, 277V	Bronze	34	15.4
WGH-400P	400w/PS	120, 208, 240, 277V	Bronze	37	16.8

¹ Lamp included on all units.

ACCESSORIES

(order as separate part #)

Catalog Number	Description
PBT-1	Photocontrol, 120 volt
PBT-234	Photocontrol, 208, 240, 277 volt
SM106-SHIELD	Polycarbonate Shield for MID-SIZE fixtures
SM106VISOR	Top visor for MID-SIZE fixtures
SM708VISOR	Top visor for LARGE fixtures

PHOTOMETRIC REPORTS

Catalog Number	Report #
WGH150S	HP09709.IES
WGH400S	HP09706.IES



HUBBELL
Outdoor Lighting

Hubbell Outdoor Lighting • 701 Millennium Boulevard • Greenville, SC 29607 • Phone: 864-678-1000

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2018 HUBBELL OUTDOOR LIGHTING, All Rights Reserved • For more information visit our website: www.hubbelloutdoor.com • Printed in USA

WGH-SPEC 3/18