




radiant Collection
radiant® Easy 3-Way Dimmer Kit, White
Part No. WNREZK50WH



This kit uses a wireless dimmer to easily add control of a light or fixture from a second location, even in rooms or locations currently without 3-way wiring. Simply replace the existing switch or dimmer with the kit's radiant® Tru-Universal Dimmer (wired), then use the included battery-powered radiant® Wireless Dimmer to add another point of control wherever it is desired. Mount the Wireless Dimmer to any wall or surface – without cutting, wiring or tools – using the provided adhesive. The dimmers come pre-paired to enable multi-location control in seconds. Want app control? These devices are equipped for enhanced functionality. Simply add a Smart Gateway with Netatmo and use the Legrand Home + Away app to control your lights from anywhere (and much more). For more information visit www.legrand.us/addappcontrol. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Easily adds control of a light from a second dimmer

Ready to install, no configuration needed

First Dimmer (Wired) Installation: Replaces any standard (wired) switch or dimmer in as little as 15 minutes. Neutral required

Second Dimmer (Wireless) Installation: Mounts to any wall for long-lasting, battery-powered control

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V)

Add a Smart Gateway with Netatmo to control lights via app, connect to other smart products and more

Screwless Wall Plates included. Coordinate with other designer switches and outlets from the radiant® Collection for a cohesive, sophisticated look

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007442687
Country Of Origin	China	Material	Polycarbonate
Features	With Netatmo	Switch Type	Paddle
Number of Switches	1	Works With	Netatmo
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Standard	RoHS, FCC, cULus
Warranty Type	1-Year Limited Warranty	Type	Dimmer, Kit

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Load Rating	120V 250W 2.1A (CFL - Reverse Phase Only), 120V 250W 2.1A (EFL - Reverse Phase Only), 120V 250W 2.1A (ELV - Reverse Phase Only), 120V 250W 2.1A (LED - Reverse Phase Only), 120V 450W (ELV - Reverse Phase Only), 120V 450W (Halogen - Reverse Phase Only), 120V 450W (Incandescent - Reverse Phase Only), 120V 450W 3.8A (CFL - Forward Phase Only), 120V 450W 3.8A (EFL - Forward Phase Only), 120V 450W 3.8A (LED - Forward Phase Only), 120V 700W (Halogen - Forward Phase Only), 120V 700W (Incandescent - Forward Phase Only)	Seismic Tested	No
-------------	---	----------------	----

Dimming Compatibility	Forward or Reverse Selectable Phase	Frequency Rating	60 Hz
-----------------------	-------------------------------------	------------------	-------

Connection	Wireless, Wired	Maximum Humidity	95% (relative humidity, non-condensing)
------------	-----------------	------------------	---

Number of Poles	Multi-Location, Single Pole 3-Way	Wire Size	#14 - #10 AWG
-----------------	-----------------------------------	-----------	---------------

Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
-----------------------	-----	----------------	--------

Mounting Type	Box, Wall	Wire Connection Type	Flying Leads
---------------	-----------	----------------------	--------------

Voltage	120 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED
Environmental Conditions	95% (relative humidity, non-condensing)		
