
WP2F84

Mid sized wallpack. All aluminum precision die cast construction with tempered glass refractor. Lamp supplied.

Color: Bronze

Weight: 10.9 lbs





Lamp Info Ballast Info

Elec HPF QT Type: 2-42W Triple Type: Watts: 84W 120V: 0.78A Shape/Size: N/A 208V: 0.5A Base: N/A 240V: 0.5A ANSI: N/A 277V: 0.33A Hours: 12,000 Input Watts: 93W Lamp Lumens: 6,400 Efficiency: 90% Efficacy: 69 LPW

Technical Specifications

UL Listing:

Suitable for wet locations. HID fixtures can be wired with 90°C supply wiring if supply wires are routed 3" away from ballast.

Housing:

Die cast aluminum, 1/2" NPS tapped holes top, both sides and back for conduit or photocontrol. Hinged refractor frame. Continuous silicone rubber gasket.

Reflector:

Specular anodized aluminum, removable for installation. Symmetrical light pattern maximizes distance between fixtures.

Cutoff Lens:

Tempered glass.

Refractor:

Prismatic optics designed to minimize glare and throw light down and out. Heat resistant borosilicate glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Ballast Minimum Starting Temperature:

0°F.