



**On-Q**  
**Category 5e RJ45 Keystone Connector, Light Almond**  
Part No. WP3450LA



Upgrade your network infrastructure with this Category 5e RJ45 Keystone Connector in light almond. The vertical design simplifies punchdown termination, while the rear retention caps ensure secure wire connections. This insert is compatible with all Keystone wall plates and meets Category 5e performance standards for reliable network performance.

## Features & Benefits

Ensures Category 6 performance standard compliance

Rear retention caps ensure secure wire termination

Vertical design for easy punchdown termination

T568A and T568B wiring labels included

Meets Category 5e described in TIA/EIA-568-B.2

Insertion and extraction life is 750 Cycles Min

Jack housing is high-impact, flame resistant plastic, UL 94V-0

Spring wire is phosphor bronze alloy plated with 50 micro-inch of gold over 100 micro-inches of nickel

Also available in contractor pack of 50 (WP3450-WH-50)

## Specifications

### General Info

Product Line	On-Q	Color	Light Almond
UPC Number	804428024866	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0

### Dimensions

Product Width US	0.64 in	Product Height US	0.87 in
Product Length US	1.28 in		

---

## Technical Information

---

Termination Style

Punchdown

Cable Type

Cat5e

---

Environmental Conditions

0 to 93% (relative humidity, non-condensing)

---



**On-Q**  
**Category 5e RJ45 Keystone Connector, Light Almond**  
Part No. WP3450LA



Upgrade your network infrastructure with this Category 5e RJ45 Keystone Connector in light almond. The vertical design simplifies punchdown termination, while the rear retention caps ensure secure wire connections. This insert is compatible with all Keystone wall plates and meets Category 5e performance standards for reliable network performance.

## Features & Benefits

Ensures Category 6 performance standard compliance

Rear retention caps ensure secure wire termination

Vertical design for easy punchdown termination

T568A and T568B wiring labels included

Meets Category 5e described in TIA/EIA-568-B.2

Insertion and extraction life is 750 Cycles Min

Jack housing is high-impact, flame resistant plastic, UL 94V-0

Spring wire is phosphor bronze alloy plated with 50 micro-inch of gold over 100 micro-inches of nickel

Also available in contractor pack of 50 (WP3450-WH-50)

## Specifications

### General Info

Product Line	On-Q	Color	Light Almond
UPC Number	804428024866	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0

### Dimensions

Product Width US	0.64 in	Product Height US	0.87 in
Product Length US	1.28 in		

---

## Technical Information

---

Termination Style	Punchdown	Cable Type	Cat5e
-------------------	-----------	------------	-------

---

Environmental Conditions	0 to 93% (relative humidity, non-condensing)
--------------------------	--

---