Pass and Seymour
Weatherproof Single Gang Box, Gray
Part No. WPB25

Weatherproof 1 Gang Box, 5 Hole 1/2, 17.0 Cu. In.,Gray (2 Holes Each End, 1 Hole in Back)

Features & Benefits

- Wide range of sizes, depths, and gangs.
- 2 closure plugs and mounting lugs furnished with all boxes.
- Designed for both interior and exterior applications.
- Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.
- For covering patents, see www.legrand.us/patents.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- UL Listed for wet and/or damp locations with appropriate cover.
- Will accept standard 4 screw mounting covers and single gang weatherproof covers.
- Heavy die-cast aluminum.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116403	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Weatherproof
Number of Knockouts	5	Application Sector	Commercial, Residential
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	2.86 in	Product Weight US	0.62 lb
Product Volume US	17.0 cu in	Product Depth US	2.09 in
Product Height US	4.63 in	Product Length US	4.63 in
Cubic Capacity	17 in^3	Box Depth	Shallow

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143223

Technical Information

Number of Gangs	1	Size of Threaded Openings	1/2 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Top
Box Shape	Rectangular	Mounting Type	Screw Mount