
THERMOPLASTIC WEATHERPROOF COVERS FOR FLANGED INLET/OUTLET

WPG2 | [Pass & Seymour](#)



FEATURES & BENEFITS

Industrial Grade Weatherproof Lift Cover, 2.32" Diameter Opening to Accommodate 20A/30A Turnlok, For Flanged Inlet/Outlet, Gray

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Stainless steel mounting screws also resist corrosion.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Covers fit all competitive inlets and outlets.
- Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.
- Tamper-proof hinge features permanent, locked-in pins for added security.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Covers
Duty: Heavy Duty
Special Features: Weatherproof

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121305
UR: No

DIMENSIONS

Height (US): 4.57"

Width (US): 2.85"

TECHNICAL INFORMATION

Amps: 20A/30A

Material: Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

