



Pass and Seymour
4-in Round Outdoor Cluster Cover, Gray
Part No. WPRB13

Weatherproof 4-inch Round Outdoor Cluster Cover, Blank 3 Hole
1/2-in With Gasket and Screws, Bronze



Features & Benefits

Wide range of rectangular and round covers.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

Kits available combining fixtures, lamp covers, and accessories.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007117110
Country Of Origin	India	Material	Aluminum
Cover Type	Weatherproof	Features	Corrosion Resistant, Weatherproof
Cover Shape	Round	Application Sector	Industrial
Standard	UL listed	Type	Weatherproof Cover

Dimensions

Product Width US	4.625 in	Product Depth US	1.0 in
Product Height US	4.625 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Number of Gangs	1	Indoor/Outdoor	Both
Mounting Type	Box Mounted	Box Cover Position	Horizontal
Number of Outlets	3		