



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WPS25 250W HPS Wal-Pak Borosilicate Glass Hinged/Removab

*Cooper Lighting Solutions*

|                  |                                                                                                |
|------------------|------------------------------------------------------------------------------------------------|
| Catalog Number   | WPS25                                                                                          |
| Manufacturer     | Cooper Lighting Solutions                                                                      |
| Description      | Wal-Pak 250W HPS Multi-Tap Borosilicate Glass Wall Mount, W/Lamp Bronze, Hinged Removable Door |
| Weight per unit  | 22.8 (lbs/each)                                                                                |
| Product Category | Lighting                                                                                       |

### Features

|                 |                      |
|-----------------|----------------------|
| amperage rating | 0.903 (at 277V)      |
| Ballast Type    | Electronic Ballast   |
| Lamp Included   | Yes                  |
| Lamp Type       | HIGH PRESSURE SODIUM |
| Material        | Die-Cast Aluminum    |
| Number of Lamps | 1                    |
| Voltage Rating  | 120-277V             |
| Wattage         | 250W                 |

### Material, Color, and Finish

|       |         |
|-------|---------|
| Style | (blank) |
|-------|---------|

### Descriptions

|                        |                                                                                                |
|------------------------|------------------------------------------------------------------------------------------------|
| Description            | 250W HPS WAL-PAK BOROSILICATE GLASS HINGED/REMOVAB                                             |
| extra long description | CLS WPS25 250W HPS MT PRISM GLASS L                                                            |
| Long Description       | Wal-Pak 250W HPS Multi-Tap Borosilicate Glass Wall Mount, w/Lamp Bronze, Hinged Removable Door |
| Product Type           | 250W HPS MT Prism Glass Lens LMP BRZ                                                           |
| Special Features       | Rugged die-cast aluminum housing and door in bronze powder-coat paint                          |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Cooper Lumark  |
| GTIN                      | 00080083541225 |
| Manufacturers Part Number | WPS25          |
| UPC                       | 080083541225   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Outdoor HID Lighting |
| Type                 | WALL MOUNT           |

### Packaging

|                 |         |
|-----------------|---------|
| Carton          | 1       |
| Weight Per each | 22.7999 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                     |
|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | lighting                                                                                                                                                                            |
| Mounting    | WALL MOUNT                                                                                                                                                                          |
| standard    | UL/cUL Listed - Wet Location;IP66 Rated;40 Degree C Ambient<br>Temperature Rating;ARRA Compliant;Title 20 Compliant;EISA<br>Compliant;LM79/LM80 Compliant;DLC Premium;BAA Compliant |