ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WT11 Wiretwist Wire Connector, WT1 Gray, 100/Box

Ideal

Catalog Number	WT11
Manufacturer	Ideal
Description	Wire Twist Connector, (3) #22 Awg Conductor Size, (2) #16 Awg Conductor Size, Gray Insulation Color, +221 °F Operating Temperature, 1 to 5 Conductors, 300 V, 0.15 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	300

Material, Color, and Finish

Color	Gray

Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT1 GRAY, 100/BOX
extra long description	IDEAL WT1-1 WIRE-TWIST CONN.,GREY,B
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance.The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing

Manufacturer Information

Brand	Buchanan
GTIN	00781789610009
UPC	781789610009

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS

Availability

minimum qty	100

Packaging

Carton	100
Package	1000
Weight Per each	0.15

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS