

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1615 North Hazel St. 71801-0000, AR Hope Phone: 870-777-4225 Fax: 870-777-4343



		À		h	Ì
	À	Ø	/		ľ
- 4				ğ	
9	ē	3	U	7	

	Catalog Number Manufacturer	WT11 Ideal
	Description	Wire Twist Connector, (3) #22 Awg Conductor Size, (2) #16 Awg Conductor Size, Gray Insulation Color, +221 °F Operating Temperature, 1 to 5 Conductors, 300 V, 0.15 LB
	Weight per unit	0.0020 (lbs/each)
ļ	Product Category	Electrical Fixture Conn ( Nuts
Feat		
	Material	Flame-retardant Polypropelene
	Voltage Rating	300
	erial, Color, and Finish Color	Gray
Desc	riptions	
	Description	WIRETWIST WIRE CONNECTOR, WT1 GRAY, 100/BOX
	extra long description	IDEAL WT1-1 WIRE-TWIST CONN.,GREY,B
	Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing
Man	ufacturer Information	
ļ	Brand	Buchanan
	GTIN	00781789610009
	UPC	781789610009
	nomies, Classifications, and Categ Category Description	ories Wire nuts
Avai	lability	
	minimum qty	100
	<b>aging</b> Carton	100
	Package	1000
	Weight Per each	0.002

1615 North Hazel St. 71801-0000, AR Hope Phone: 870-777-4225 Fax: 870-777-4343

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors		
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221		
	F)		
standard	CSA C22.2 #188, UL 486C Listed, RoHS		