



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street  
71901-0000, AR Hot Springs  
Phone: 501-762-8210  
Fax: 501-762-8211



## WT31 Wiretwist Wire Connector, WT3 Orange, 100/Box

*Ideal*

Catalog Number	WT31
Manufacturer	Ideal
Description	Wire Twist Connector, (2) #18 Awg Conductor Size, (2) #14 Awg Conductor Size, Orange Insulation Color, +221 °F Operating Temperature, 3 to 5 Conductors, 600 V Ac
Weight per unit	0.2600 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

### Material, Color, and Finish

Color	Orange
-------	--------

### Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT3 ORANGE, 100/BOX
extra long description	IDEAL WT3-1 WIRE-TWIST CONN.,ORANGE
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing

### Manufacturer Information

Brand	Buchanan
GTIN	00781789610047
UPC	781789610047

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

### Availability

minimum qty	100
-------------	-----

### Packaging

Carton	100
Package	1000
Weight Per each	0.26



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street  
71901-0000, AR Hot Springs  
Phone: 501-762-8210  
Fax: 501-762-8211

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS