



WT41B Wingtwist Wire Connector, WT41 Tan, 500/Bag

Ideal

| | |
|------------------|---|
| Catalog Number | WT41B |
| Manufacturer | Ideal |
| Description | Buchanan, Wire Connector, Wingtwist, Conductor Range: 22 - 10 Awg, 2/20 Awg Min, 3/10 Solid Awg Max, Number Of Conductors: 1 to 6, Material: Flame-Retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT41 |
| Weight per unit | 0.0040 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|-------------------------------|
| Material | Flame-retardant Polypropelene |
| media | Yes |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Tan |
|-------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | WINGTWIST WIRE CONNECTOR, WT41 TAN, 500/BAG |
| extra long description | IDEAL WT41-B WINGTWIST WT41 TAN, 50 |
| Features | With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote |
| Long Description | Buchanan, Wire Connector, WingTwist, Conductor Range: 22 - 10 AWG, 2/20 AWG Min, 3/10 Solid AWG MAX, Number Of Conductors: 1 to 6, Material: Flame-retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT41 |
| Product Type | Wingtwist WT41 Tan, 500 Bag |
| Special Features | 1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip;Green Model Designed For Ground Connections;Model Number: WT41;UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified;Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum E |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00781789967677 |
| Manufacturers Part Number | WT41-B |
| UPC | 781789967677 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
|----------------------|-----------|

Availability

| | |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 500 |
| Package | 5000 |
| Weight Per each | 0.004 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Insulating or Joining 1 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA C22.2 #188, UL 486C Listed, RoHS |