

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street 72701-0000, AR Fayetteville Phone: 479-443-4948 Fax: 479-443-6465



WT4B Wiretwist Wire Connector, WT4 Yellow, 500/Bag

Catalog Number	WT4B
Manufacturer	ldeal
Description	Buchanan, Wire Connector, Wiretwist, Conductor Range: 18 - 10 Awg, 3/18 Awg Min, 4/14 Awg Max With 1/18, Number Of Conductors: 2 to 5, Material: Flame-Retardant Polypropelene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT4
Weight per unit	0.0030 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts
Features	
Material	Flame-retardant Polypropelene
Voltage Rating	600
Material, Color, and Finish	
Color	Yellow



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street 72701-0000, AR Fayetteville Phone: 479-443-4948 Fax: 479-443-6465

ъ.				
	SCI	nni	\mathbf{r}	nc
	- N I			
\mathbf{r}	, 301	IN	$\cdot \cdot \cdot \cdot$	113
		-		_

Description	WIRETWIST WIRE CONNECTOR, WT4 YELLOW, 500/BAG
extra long description	IDEAL WT4-B WIRE-TWIST CONN.,YELLOW
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing
Long Description	Buchanan, Wire Connector, WireTwist, Conductor Range: 18 - 10 AWG, 3/18 AWG Min, 4/14 AWG MAX With 1/18, Number Of Conductors: 2 to 5, Material: Flame-retardant Polypropelene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT4
Product Type	Wire-Twist Conn., Yellow, Bag500
Special Features	1,000V Maximum In Fixtures And Signs; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip; Model Number: WT4; Ribbed Cap Provides Positive Grip For Fast, Easy Installation; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F); UL 486C Listed And CSA 22.2 #188 Certified
anufacturer Information	

Brand	Buchanan	
GTIN	00781789610078	
Manufacturers Part Number	WT4-B	
UPC	781789610078	

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

Availability

minimum qty 500

Packaging

Carton	10000
Weight Per each	0.003

555 E. 15th Street 72701-0000, AR Fayetteville Phone: 479-443-4948 Fax: 479-443-6465

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221
	F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS