

# Product Specifications



## 3/16" x 1-1/4" Phillips Pan Head Wall Twister Kit

**Part Number** WTKPH  
**Category Number** 4731  
**UPC** 781002857662

The Wall Twister® is an all steel, single piece screw anchor manufactured with a unique deep cutting thread design, its suitable for fastening objects into drywall, wood, concrete, plaster, brick, and block walls. The patented reverse serrations under the head prevent over-torquing. When working with masonry-based materials, use the 3/16 carbide tipped drill bit included in the kit to create a pilot hole. When fastening into drywall or wood, no pre-drilling is required. Typical applications include HVAC fixtures, signs, telecommunications equipment, plumbing fixtures, and many more.



### Physical Characteristics

<b>Bit</b>	IB2PL
<b>Anchor Type</b>	Wall Twister
<b>Drive Type</b>	Phillips
<b>Head Type</b>	Pan
<b>Thread Style</b>	Helical
<b>Size</b>	3/16" x 1-1/4"
<b>Anchor Diameter</b>	1/4"
<b>Anchor Length</b>	1-1/4"
<b>Material</b>	AISI 1018 Carbon Steel
<b>Finish</b>	Zinc Plated
<b>Number of Pieces</b>	102
<b>Installation</b>	No Pre-Drilling Required for Wallboard and Plywood, Pre-Drilling Required For Concrete, Hollow or Grout Filled Block, Brick and Plaster

### Performance Data

<b>Pre-Drill Size</b>	3/16"
<b>Applications</b>	Wallboard, Plywood, Concrete, Hollow or Grout Filled Block, Brick and Plaster
<b>Special Features</b>	All Steel Single Piece Screw Anchor, Reverse Serrations Prevent Over Torquing, Heat Treated Point, High Profile Threads, Resists Wobble/Stripping, Can Be Removed

### Packaging Details

<b>Kit Contains</b>	(100) Phillips Pan Head Wall Twisters, (1) 3/16" Carbide Tipped Drill Bit, (1) #2 Phillips Power Bit
<b>Standard Qty</b>	1
<b>Master Qty</b>	10
<b>Price Per</b>	1
<b>Package Length</b>	7.50
<b>Package Width</b>	3.40
<b>Package Height</b>	1.30
<b>Net Weight</b>	0.96
<b>Package Weight</b>	.96
<b>Package Type</b>	Two Compartment Box

### Certifications

<b>RoHS Compliant</b>	Yes
-----------------------	-----