

Product Specifications



3/16" x 1-1/4" White Phillips Pan Head Wall Twister Kit

Part Number WTKWT
Category Number 4731
UPC 781002857679

The Wall Twister® is an all steel, single piece screw anchor manufactured with a unique deep cutting thread design, its suitable for fastening objects into drywall, wood, concrete, plaster, brick, and block walls. The patented reverse serrations under the head prevent over-torquing. When working with masonry-based materials, use the 3/16 carbide tipped drill bit included in the kit to create a pilot hole. When fastening into drywall or wood, no pre-drilling is required. Typical applications include HVAC fixtures, signs, telecommunications equipment, plumbing fixtures, and many more.



Physical Characteristics

Bit	IB2PL
Anchor Type	Wall Twister
Drive Type	Phillips
Head Type	Wafer
Thread Style	Helical
Size	3/16" x 1-1/4"
Anchor Diameter	1/4"
Anchor Length	1-1/4"
Material	AISI 1018 Carbon Steel
Finish	Zinc Plated
Number of Pieces	102
Installation	No Pre-Drilling Required for Wallboard and Plywood, Pre-Drilling Required For Concrete, Hollow or Grout Filled Block, Brick and Plaster

Performance Data

Pre-Drill Size	3/16"
Applications	Wallboard, Plywood, Concrete, Hollow or Grout Filled Block, Brick and Plaster
Special Features	All Steel Single Piece Screw Anchor, Reverse Serrations Prevent Over Torquing, Heat Treated Point, High Profile Threads, Resists Wobble/Stripping, Can Be Removed

Packaging Details

Kit Contains	(100) Phillips Wafer Head Wall Twister Kit, (1) 3/16" Carbide Tipped Drill Bit, (1) #2 Phillips Power Bit
Standard Qty	1
Master Qty	10
Price Per	1
Package Length	7.50
Package Width	3.40
Package Height	1.30
Net Weight	0.955
Package Weight	.96
Package Type	Two Compartment Box

Certifications

RoHS Compliant	Yes
----------------	-----