



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWHR15 High Volt Rubberless Tape 30 FTX 1.5 In

Nsi Industries

Catalog Number	WWHR15
Manufacturer	Nsi Industries
Description	Warriorwrap WW-HR-15 Black High-Voltage Linerless Rubber Splicing Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 30MIL Thick, 1.5 Inch Wide, 30FT Long and Has An Ethylene Rubber-Based Design. The Self-Bonding Adhesive Helps Stick to Uneven Surfaces and Easily Conforms to Irregular Shapes. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Insulating, Jacketing Of Splices On Power Cables, Jacketing Terminati
Weight per unit	0.3870 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

Features

maximum voltage	69
Temperature Range	130 C, 266 F
Tensile Strength	333.6
Warranty	1 YEAR

Material, Color, and Finish

Backing Material	NSI
------------------	-----

Dimensions and Weight

Length	30
Thickness	30
Width	1.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	HIGH VOLT RUBBERLESS TAPE 30 FTX 1.5 IN
extra long description	NSI WW-HR-15 Warrior Wrap High Volt
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity. This high-voltage linerless rubber splicing tape can handle the toughest jobs, like the insulation and jacketing of splices on power cables from 600-Volt up to 69,000 Volt. The self
Long Description	WarriorWrap WW-HR-15 Black High-Voltage Linerless Rubber Splicing Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 30mil thick, 1.5 inch wide, 30ft long and has an ethylene rubber-based design. The self-bonding adhesive helps stick to uneven surfaces and easily conforms to irregular shapes. Top breaking strength and elasticity make WarriorWrap an excellent choice for insulating, jacketing of splices on power cables, jacketing terminati
Product Type	Warrior Wrap High Voltage 69KV Linerless Rubber Splicing Tap

Manufacturer Information

Brand	WarriorWrap
GTIN	00662381365606
Manufacturers Part Number	WW-HR-15
UPC	662381365606

Taxonomies, Classifications, and Categories

Category Description	TAPE
----------------------	------

Packaging

Carton	1
Weight Per each	0.387