




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWSR10 High Voltage Silicone Rubber 30 FT X 1 In

Nsi Industries

Catalog Number	WWSR10
Manufacturer	Nsi Industries
Description	Warriorwrap WW-SR-10 Gray Silicone Rubber High-Voltage Splicing Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 20MIL Thick, 1 Inch Wide, 30FT Long and Is Made From Silicone Rubber. The Self-Bonding Design Features No Adhesive But Forms A Solid Mass When Wrapped Under Tension. Top Breaking Strength, Elongation and Elasticity Make Warriorwrap An Excellent Choice For Heavy-Duty Jobs Including Jacketing High-Voltage Terminations On Extru
Weight per unit	0.1600 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

Features

Material	SILICONE RUBBER
maximum voltage	69
Temperature Range	180 C, 356 F
Tensile Strength	580
Warranty	1 YEAR

Material, Color, and Finish

Backing Material	NSI
Color	Light Grey

Dimensions and Weight

Length	30
Size	L=30 FT - W=1.00 IN
Thickness	20
Width	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	HIGH VOLTAGE SILICONE RUBBER 30 FT X 1 IN
extra long description	NSI WW-SR-10 Silicone Rubber Tape H
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity. This silicone rubber splicing tape is a self-amalgamating, chemically cross-linked tape that self-bonds when wrapped under tension and forms a solid mass within minutes of applicati
Long Description	WarriorWrap WW-SR-10 Gray Silicone Rubber High-Voltage Splicing Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 20mil thick, 1 inch wide, 30ft long and is made from silicone rubber. The self-bonding design features no adhesive but forms a solid mass when wrapped under tension. Top breaking strength, elongation and elasticity make WarriorWrap an excellent choice for heavy-duty jobs including jacketing high-voltage terminations on extru
Product Type	Silicone Rubber Tape HV 1" 30FT
Special Features	Unique triangular cross-section, Self-amalgamating, UV and Oil resistant, Center line for half-lapping guide

Manufacturer Information

Brand	NSi
GTIN	00662381365705
Manufacturers Part Number	WW-SR-10
UPC	662381365705

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Silicone Rubber

Packaging

Carton	1
Weight Per each	0.16

Uses, Certifications, and Standards

Application	For jacketing of high voltage terminations on extruded dielectric cables through 69000 volts. For insulating high temperature silicone insulated cables. A positive oil stop in the construction of transition splices.
-------------	---