



Powering Business Worldwide

pe.eaton.com

HVX 9000 Enclosed Drive

HVX02514BARB

UPC:782116587551

Dimensions:

- **Height:** 30.25 IN
- **Length:** 15.02 IN
- **Width:** 7.5 IN

Weight:67 LB

Notes:HOA Keypad is included ad the standard control panel. Some options are voltage and/or horsepower specific. Consult your Eaton representative fot details.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Brake Chopper:** Brake chopper
- **Options:** Manual IOB Bypass Controller
- **Amperage Rating:** 38A
- **Enclosure:** NEMA 1, Enclosed Drive
- **Enclosure Size:** 1
- **Frame Size:** 6
- **Horsepower:** 25 hp
- **Type:** HVX Drive
- **Voltage Rating:** 480V

Supporting documents:

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Eaton Specification Sheet - HVX02514BARB](#)

Certifications:

- UL Listed

Product compliance: No Data



