

# Eaton HVX02514BARB

Catalog Number: HVX02514BARB

HVX 9000 Enclosed Drive, 25 hp, NEMA 1, 480V, Internal brake chopper, Options: Manual IOB Bypass Controller, Frame size 6, 38A, Enclosure size 1



Photo is representative

## General specifications

### Product Name

Eaton HVX9000 enclosed variable frequency drive

### Catalog Number

HVX02514BARB

### UPC

782116587551

### Product Length/Depth

15.02 in

### Product Height

30.25 in

### Product Width

7.5 in

### Product Weight

67 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

HOA Keypad is included as the standard control panel. Some options are voltage and/or horsepower specific. Consult your Eaton representative for details.

## defaultTaxonomyAttributeLabel

### Brake chopper

Brake chopper

### Amperage Rating

38A

### Horsepower

25 hp

### Type

HVX Drive

### Voltage rating

480 V

### Frame size

FR6

### Options

Manual IOB bypass controller

### Enclosure

NEMA 1

### Enclosure size

1

## Resources

### Brochures

[Variable frequency drive - Product overview](#)

### Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - HVX02514BARB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)