



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## XT0B070GC1 IEC Ovlr Frame G Class 10 50-70a

Eaton Corp

|                  |                                                                                                                                                                                                                                                         |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | XT0B070GC1                                                                                                                                                                                                                                              |
| Manufacturer     | Eaton Corp                                                                                                                                                                                                                                              |
| Description      | Overload Relay, Bi-Metallic, Thermal Type; 690 Volt Ac 6 Amp Contact Rating; UL, Csa, Ce Approval; Contactor Mounting; IP20 Enclosure; Screw Terminal Type; 1NO-1NC Auxiliary Contact; 3 Nema Size; 50 to 70 Amp Motor Fla; Automatic/Manual Reset Type |
| Weight per unit  | 2.9 (lbs/each)                                                                                                                                                                                                                                          |
| Product Category | Overload Relays & Accessories                                                                                                                                                                                                                           |

### Features

|                     |                   |
|---------------------|-------------------|
| Ambient Temperature | COMPENSATED       |
| Auxiliary Contact   | 1NO-1NC           |
| Contact Rating      | 690 Volt AC 6 Amp |
| IEC Size            | F, G              |
| Motor FLA           | 50 to 70 Amp      |
| Reset Type          | Automatic/Manual  |
| Terminal Type       | Screw             |
| Trip Class          | CLASS 10A         |

### Descriptions

|                        |                                                                                                                                                                                                                                                                        |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Information | NEMA RoHS/ATEX Compliant; Overall Dimension 4.65 Inch Width x 5.43 Inch Depth x 5.28 Inch Height                                                                                                                                                                       |
| Commodity Description  | OVERLOAD RELAYS & ACCESSORIES                                                                                                                                                                                                                                          |
| Description            | IEC OVLR FRAME G CLASS 10 50-70A                                                                                                                                                                                                                                       |
| extra long description | BIMETALLIC TYPE; UL, CSA APPROVAL; CONTACTOR MOUNTING; 1NO-1NC AUXILIARY CONTACT; 50 TO 70 AMPERE MOTOR FLA; CLASS 10A TRIP CLASS; ROHS COMPLIANT; FRAME SIZE 90 MM; USED ON 80 TO 170 AMPERE CONTACTOR; APPLICABLE STANDARD IEC 60947, EN 60947, CE, ATEX; XTOB MODEL |
| Long Description       | OVERLOAD RELAY, BI-METALLIC, THERMAL TYPE; 690 VOLT AC 6 AMP CONTACT RATING; UL, CSA, CE APPROVAL; CONTACTOR MOUNTING; IP20 ENCLOSURE; SCREW TERMINAL TYPE; 1NO-1NC AUXILIARY CONTACT; 3 NEMA SIZE; 50 TO 70 AMP MOTOR FLA; AUTOMATIC/MANUAL RESET TYPE                |
| Product Type           | Overload Relay                                                                                                                                                                                                                                                         |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | EATON CUTLER-HAMMER |
| GTIN                      | 04015082784638      |
| Manufacturers Part Number | XTOB070GC1          |
| Model                     | XTOB                |
| UPC                       | 015082784632        |

## Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | IEC/FREEDOM CONTACTOR |
| Type                 | Bi-Metallic, Thermal  |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 2.9 |

## Uses, Certifications, and Standards

|           |             |
|-----------|-------------|
| Approval  | UL, CSA, CE |
| Enclosure | IP20        |
| Mounting  | CONTACTOR   |
| NEMA Size | 3 in        |