



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XTCE009B10A Contactor 3P FVNR 9A Frame B 1NO 110/50 120/60 Coi *Eaton Corp*

Catalog Number	XTCE009B10A
Manufacturer	Eaton Corp
Description	Magnetic Contactor, Full Voltage, Non-Reversing Type; Frame 45 Millimeter Size; UL, Csa, Ce Approval; IP20 Enclosure; 20 Amp (UL Continuous), 9 Amp (Ac-3), 22 Amp (Ac-1) Current Rating; 3 Pole(S); IEC Construction Standard
Weight per unit	0.5000 (lbs/each)
Product Category	IEC Contactors

Features

Auxiliary Contact	1NO
Coil Voltage	110 Volt AC at 50 Hertz, 120 Volt AC at 60 Hertz
Construction Standard	IEC
Current Rating	20 Amp (UL Continuous), 9 Amp (AC-3), 22 Amp (AC-1)
Poles	3 in
Power Rating/Voltage	1/2 HP at 115 Volt 1-Phase, 1 HP at 200 Volt 1-Phase, 1-1/2 HP at 230 Volt 1-Phase, 3 HP at 200/230 Volt 3-Phase, 5 HP at 460 Volt 3-Phase, 7-1/2 HP at 575 Volt 3-Phase (UL/CSA Rating), 2.5 Kilowatt at 220/230 Volt 50/60 Hertz 3-Phase, 4 Kilowatt at 380/4

Dimensions and Weight

Size	Frame 45 Millimeter
------	---------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Temperature Rating -25 to 50 Deg C
Commodity Description	IEC CONTACTORS
Description	CONTACTOR 3P FVNR 9A FRAME B 1NO 110/50 120/60 COI
extra long description	FULL VOLTAGE, NON-REVERSING TYPE; FRAME 45 MILLIMETER SIZE; UL, CSA, CE APPROVAL; IP20 ENCLOSURE; 20 AMP (UL CONTINUOUS), 9 AMP (AC-3), 22 AMP (AC-1) CURRENT RATING; 3 POLE(S); IEC CONSTRUCTION STANDARD; 110 VOLT AC AT 50 HERTZ, 120 VOLT AC AT 60 HERTZ COIL VOLTAGE; 1NO AUXILIARY CONTACT; 1/2 HP AT 115 VOLT 1-PHASE, 1 HP AT 200 VOLT 1-PHASE, 1-1/2 HP AT 230 VOLT 1-PHASE, 3 HP AT 200/230 VOLT 3-PHASE, 5 HP AT 460 VOLT 3-PHASE, 7-1/2 HP AT 575 VOLT 3-PHASE (UL/CSA RATING), 2.5 KILOWATT AT 220/230 VOLT 50/60
Long Description	MAGNETIC CONTACTOR, FULL VOLTAGE, NON-REVERSING TYPE; FRAME 45 MILLIMETER SIZE; UL, CSA, CE APPROVAL; IP20 ENCLOSURE; 20 AMP (UL CONTINUOUS), 9 AMP (AC-3), 22 AMP (AC-1) CURRENT RATING; 3 POLE(S); IEC CONSTRUCTION STANDARD
Product Type	Magnetic Contactor

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	04015082766870
Manufacturers Part Number	XTCE009B10A
Model	XT
UPC	015082766874

Taxonomies, Classifications, and Categories

Category Description	IEC/FREEDOM CONTACTOR
Type	Full Voltage, Non-Reversing

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

Approval	UL, CSA, CE
Enclosure	IP20