

Eaton XT IEC contactor

XTCE065DS1A

UPC:786685365121

Dimensions:

- **Height:** 1 IN
- **Length:** 1 IN
- **Width:** 1 IN

Weight:1 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 65A
- **Coil:** 110V 50 Hz, 120V 60 Hz
- **Coil Voltage:** 110 Vac 50 Hz, 120 Vac, 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 5, 10, 15/ 20, 25, 50, 60 hp
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_D 2D PDF](#)
- [XTCE_D 2D Drawing Xchange](#)
- [XTCE_D 3D Inventor](#)
- [XTCE_D AutoCAD 2D Footprint](#)
- [XTCE_D 3D Model Xchange](#)
- [Eaton Specification Sheet - XTCE065DS1A](#)



Certifications:

- CSA Certified
- UL Listed
- EN 60947
- IEC 60947

Product compliance: No Data

© 2016 Eaton. All rights reserved.