

Eaton XTCR040D11A

Catalog Number: XTCR040D11A

Eaton XT IEC contactor, 40A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 40A, Frame D, 55 mm, 50-60 Hz, 3, 7.5/ 10, 15, 30, 40 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specifications



Product Name
Eaton XT IEC contactor

Catalog Number
XTCR040D11A

UPC
786685180250

Product Length/Depth
9.5 in

Product Height
6 in

Product Width
6.5 in

Product Weight
4.7 lb

Compliances
CE Marked
RoHS Compliant

Certifications
UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Notes
Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

40A

HP rating - max

3, 7.5/ 10, 15, 30, 40 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

40 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_D 3D Model Xchange](#)

[XTCR_D AutoCAD 2D Footprint](#)

[XTCR_D 2D PDF](#)

[XTCR_D 3D Inventor](#)

[XTCR_D AutoCAD 2D Footprint \(mm\)](#)

[XTCR_D 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR040D11A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)